

AC DIGITAL CLAMP METER KEW 2200R / 2200



KEW 2200R / 2200 Specifications


	KEW 2200R	KEW 2200
Detection method	RMS	Averaging value
AC A	40.00/400.0/1000A(Auto-ranging) ±1.5%rdg±5dgt(45~65Hz) ±2.0%rdg±5dgt(40Hz~1kHz)	40.00/400.0/1000A(Auto-ranging) ±1.4%rdg±6dgt(50/60Hz) ±1.6%rdg±6dgt(45~65Hz)
AC V	4.000/40.00/400.0/600V(Auto-ranging) ±1.8%rdg±7dgt(45~65Hz) ±2.3%rdg±8dgt(65~500Hz)	
DC V	400.0mV/4.000/40.00/400.0/600V(Auto-ranging) ±1.0%rdg±3dgt* *400mV range is excluded	
Ω	400.0Ω/4.000/40.00/400.0kΩ/4.000/40.00MΩ(Auto-ranging) ±2.0%rdg±4dgt(0~400kΩ) ±4.0%rdg±4dgt(4MΩ) ±8.0%rdg±4dgt(40MΩ)	
Continuity buzzer	buzzer sounds below 50±30Ω	
Conductor size	φ33mm max.	
Applicable standards	IEC61010-1 CATIV300V*, CATIII600V Pollution degree2(AC A) *2200R only CATIII300V, CATII600V Pollution degree2(AC/DC V) IEC61010-031, IEC61010-2-032, IEC61326(EMC), EN50581(RoHS)	
Power source	R03/LR03(AAA)(1.5V)×2	
Continuous measuring time	Approx.120 hours	Approx.350 hours
	Auto power off : approx.10 minutes	
Dimensions/Weight	190(L)x68(W)x20(D)mm / Approx.120g(including batteries)	
Accessories	7107A (Test leads), 9160 (Carrying case), R03(AAA)×2, Instruction manual	
Optional	8008 (Multi-tran)	

Reliable result can be obtained even from distorted wave form generated by nowadays electronic loads Averaging value type Waveform √correct √correct reading reading √correct higher reading reading √correct lower reading reading √correct lower reading reading


Accessories


















Safety Warnings:

Please read the "Safety Warnings" in the instruction manual supplied with the instrument thoroughly and completely for correct use. Failure to follow the safety rules can cause fire, trouble, electrical shock, etc. Therefore, make sure to operate the instrument on a correct power supply and voltage rating marked on each instrument.

For inquires or orders:



KYORITSU ELECTRICAL **INSTRUMENTS** WORKS, LTD.

2-5-20, Nakane, Meguro-ku, Tokyo, 152-0031 Japan Phone:+81-3-3723-0131 Fax:+81-3-3723-0152 E-mail:info-eng@kew-ltd.co.jp

http://www.kew-ltd.co.jp

